

Microscope cameras KERN ODC

Specialists in microscopy for measurement, counting, documentation, archiving and image processing

Features

- A large selection of microscope cameras is available for your individual applications
- The universal microscope cameras can be used anywhere and can be connected to the microscope as well as to a laptop or PC using the USB cable (USB 2.0 or USB 3.0, see table)
- The power supply is through the USB cable, which means that no additional power supply is required
- Your daily work is made significantly easier with the very best synchronisation, a high frame rate as well as stable image performance together with our camera software microscope VIS KERN OXM 901 which we deliver with the product
- For details about our software please refer to the "Camera software microscope VIS KERN OXM 901" product group in the catalogue (page 90) or on the internet.
- These universal cameras can also be connected to all microscopes available on the market offering the appropriate C-mount adapter for the particular microscope

Accessories

 Object micrometer, for calibrating the software measuring function, division 0.01 mm, KERN ODC-A2403

C-mount cameras - USB 2.0/3.0 KERN ODC-82 · ODC-83



Features

- Through the proven CMOS technology, in connection with the USB 2.0 or USB 3.0 the images are shown quickly and clearly
- These cameras are also ideal for more demanding applications, such as, for example, darkfield, phase contrast and for fluorescence applications
- As well as the camera, the delivery includes our multi-lingual camera software Microscope VIS Basic KERN OXM 901, a USB cable (length: 2 m) various eyepiece adapters and an object micrometer to calibrate the software
- Please order the appropriate C-mount adapter to fit your KERN microscope now



Model KERN	Resolution	Interface	FPS	Sensor	Sensor size	Colour/ Monochrome	Supported operating system	
ODC 824	3,1 MP	USB 2.0	11,5 - 45	CMOS	1/2"	colour	Win XP, Vista, 7, 8, 10	
ODC 825	5,1 MP	USB 2.0	6,8 – 55	CMOS	1/2,5"	colour	Win XP, Vista, 7, 8, 10	
ODC 831	3,1 MP	USB 3.0	27,3 - 53,3	CMOS	1/3"	colour	Win XP, Vista, 7, 8, 10	
ODC 832	5,1 MP	USB 3.0	14,2 - 101,2	CMOS	1/2,5"	colour	Win XP, Vista, 7, 8, 10	

C-mount camera - High resolution KERN ODC-84



Features

- The high-resolution, professional ODC-84 range offers you an impressive 20 megapixel resolution which will give you bright detailed views of your sample. By using the integrated USB 3.0 interface, live images are transferred to the KERN OXM 902 for processing and documentation
- Power supply is through the USB interface so that there is no requirement for an external power source.
- As well as the camera, the delivery includes our multi-lingual camera software Microscope VIS Pro KERN OXM 902, a USB cable (length: 2 m), various eyepiece adapters and an object micrometre to calibrate the software
- Please order the appropriate C-mount adapter (only 1,0× possible) to fit your KERN microscope now

Can only be used in combination with compound microscopes



Model	Resolution	Interface	FPS	Sensor	Sensor size	Colour/ Monochrome	Supported operating system	
KERN								
ODC 841	20 MP	USB 3.0	15 – 60	CMOS	1"	colour	Win XP, Vista, 7, 8, 10	



Pictograms



360° rotatable





Monocular Microscope

For the inspection with one eye



Binocular Microscope

For the inspection with both eyes



Trinocular Microscope

For the inspection with both eyes and the additional option for the connection of a camera



Abbe Condenser

With high numerical aperture for the concentration and the focusing of light



Halogen illumination

For pictures bright and rich in contrast



LED illumination

Cold, energy-saving and especially long-life illumination



Incident illumination

For non-transparent objects



Transmitting illumination

For transparent objects



Fluorescence illumination

For stereomicroscopes




Fluorescence illumination

for compound microscopes USB 2.0 With 100W mercury lamp and filter



Fluorescence illumination for compound microscopes

With 3 W LED illumination and filter



Phase contrast unit



Darkfield condenser/unit

For a higher contrast due to indirect illumination



Polarising unit

To polarise the light



Infinity system

Infinity corrected optical system



Zoom magnification For stereomicroscopes

Auto-focus

For automatic control of the focus level



Parallel optical system

For stereomicroscopes, enables fatigue-proof working



Integrated scale

In the eyepiece



SD card

For data storage



USB 2.0 digital camera

For direct transmitting of the picture to a PC



USB 3.0 digital camera

For direct transmitting of the picture to a PC



WLAN data interface

For transmitting of the picture to a mobile display device



HDMI digital camera

For direct transmitting of the picture to a display



PC software

To transfer the measurements from the device to a PC



Automatic temperature compesation

For measurements between 10 °C and 30 °C



Protection against dust and water splashes

IPxx: The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013



Battery operation

Ready for battery operation. The battery type is specified for each device.



Battery operation rechargeable

Prepared for a rechargeable battery operation



Plug-in power supply

230V/50Hz in standard version for EU. On request GB, AUS or USA version.



Integrated power supply unit

Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.



Package shipment

The time required to manufacture the product internally is shown in days in the pictogram.

Abbreviations

Adapter for the connection of a C-Mount

Frames per second

camera to a trinocular microscope

LWD

N.A.

Long Working Distance

Numerical Aperture

SWF

Super Wide Field (Field number at least Ø 23 mm for 10× eyepiece)

W.D.

Working Distance

H(S)WF

FPS

High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses)

SLR camera Single-Lens Reflex camera

WF

Wide Field (Field number up to Ø 22 mm for 10× eyepiece)

Your KERN specialist dealer: