


Mechanical personal floor scale KERN MGC



HOME CARE





The classic robust scale for to measure body weight quickly

Features

- · Timeless design
- · Robust construction
- 1 Large, clear circular scale which is easy to read
- 2 Large platform with non-slip surface made of plastic
- Secure and non-slip positioning with rubber feet
- Easy to operate:
 simply tap on it stand on it read the weight
- Easy adjustment of the display using the setting wheel
- Note: The models are only delivered in a set of 5 units. I.e. the price given in the table refers to a delivery of 5 items. Cannot be delivered individually.

Technical data

- · Digit height 8 mm
- Overall dimensions W×D×H 285×425×85 mm
- Net weight approx. 3,1 kg

Accessories

• Cleaning cloths, alcohol-free cloths for wipe disinfectant, quick-acting, on basis of modern quaternary ammonium compounds, and also against papova viruses. Particularly gentle on materials, and therefore very well suited for the disinfection of alcohol sensitive medical products. Fulfill the legal requirements for occupational safety in accordance with TRGS 525/540. Packaging contents 80 pcs., size 20×22 cm per cloth KERN MYC-01

STANDARD 1 DAY

Model	Weighing range	Readout	
KERN	[Max] kg	[d] kg	
MGC 100K-1S05	150	1	

KERN

Pictograms



Adjusting program CAL:

For quick setting up of the balance's accuracy. External adjusting weight required.



Data interface RS-232:

To connect the balance to a printer, PC or network.



RS-485 data interface:

To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible



Bluetooth* data interface:

To transfer data from the balance to a printer, PC or other peripherals.



Control outputs (optocoupler, digital I/O):

To connect relays, signal lamps, valves, etc.



Statistics:

using the saved values, the device calculates statistical data, such as average value, standard deviation etc.



PC Software:

to transfer the measurements from the device to a PC.



Wireless data transfer:

between the weighing unit and the evaluation unit using an integrated radio module.



GLP/ISO log:

With date and time.
Only with KERN printers.



Piece counting:

Reference quantities selectable. Display can be switched from piece to weight.



Totalising level A:

The weights of similar items can be added together and the total can be printed out.



Weighing units:

Can be switched to e.g. nonmetric units at the touch of a key. Please refer to website for more details.



Weighing with tolerance range:

(Check weighing) Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model



Hold function:

When patients do not stand, sit or lie completely still, a stable weight is calculated using an average weight.



Hold function:

When the weighing conditions are unstable, a stable weight is calculated as an average value



Protection against dust and water

splashes IPxx: The type of protection is shown in the pictogram



Stainless steel:

The balance is protected against corrosion



Suspended weighing:

Load support with hook on the underside of the balance.



Battery operation:

Ready for battery operation. The battery type is specified for each device



Rechargeable battery pack:

Rechargeable set



Battery operation rechargable

Prepared for a rechargable battery operation



Universal mains adapter:

with universal input and optional input socket adapters for A) EU, GB; C) EU, GB, CH, USA, AUS.



Mains adapter:

230V/50Hz in standard version for EU. On request GB, AUS or USA version available.



Power supply:

Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.



Weighing principle: Strain gauges

Electrical resistor on an elastic deforming body.



Peak hold function:

capturing a peak value within a measuring process.



Push and Pull:

the measuring device can capture tension and compression forces.



Integrated scale:

In the eyepiece



360° rotatable microscope head

Monocular Microscope:
For the inspection with one eye.



Binocular Microscope:

For the inspection with both eyes



Trinocular Microscope:

For the inspection with both eyes and the additional option for the connection of a camera



Abbe Condenser:

With high numerical aperture for the concentration and the focusing of light



Halogen illumination:

For pictures bright and rich in contrast



LED illumination:

Cold, energy saving and especially long-life illumination



Fluorescence illumination for compound microscopes:

With 100 W mercury lamp and filter



Fluorescence illumination for compound microscopes:

With 3W LED illumination and filter



Phase contrast unit:

For a higher contrast



Darkfield condenser/unit:

For a higher contrast due to indirect illumination



Polarising unit:

To polarise the light



Infinity system:

Infinity corrected optical system



Automatic temperature compesation:

For measurements between 10 °C and 30 °C



Verification possible:

The time required for verification is specified in the pictogram.



Package shipment:

The time required for internal shipping preparations is shown in days in the pictogram.



Pallet shipment:

The time required for internal shipping preparations is shown in days in the pictogram.

Your KERN specialist dealer

^{*}The Bluetooth* word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners.